

## Frodingham 2 N Sheet Pile Interlocks

Use Adeka Ultra Seal A-30 to effectively and efficiently seal interlocks against water penetration.

One gallon of A-30 will treat approximately 140' - 150' of this interlock.



Figure # 1

Female Interlock

Apply A-30 2~3 mm deep in female socket




Figure #2

Open center interlock

Fill Completely




Figure #3

Call (800) 999-3959  
for your local  
Representative or visit  
our web site at  
[www.adeka.com](http://www.adeka.com)