



440 COVE BASE Adhesive

**Use for commercial and residential installations
of rubber and vinyl cove base.**

- Aggressive initial grab
- No open time required
- Plasticizer migration resistant
- Easy cleanup with water
- Easy to use, easy to trowel
- Zero VOC



1/8" x 1/8" x 1/8" Sawtooth
3 x 3 x 3 mm Sawtooth

2 1/2" Cove Base:

1240-1360 lin. ft./4 gal
310-340 lin. ft./gal
77-85 lin. ft./quart
72-79 lin. ft./30 oz cartridge
26-29 lin. ft./11 oz cartridge

4" Cove Base:

880-960 lin. ft./4 gal
220-240 lin. ft./gal
55-60 lin. ft./quart
51-56 lin. ft./30 oz cartridge
18-20 lin. ft./11 oz cartridge

6" Cove Base:

660-720 lin. ft./4 gal
165-180 lin. ft./gal
41-45 lin. ft./quart
38-42 lin. ft./30 oz cartridge
14-15 lin. ft./11 oz cartridge

HENRY® 440

Cove Base Adhesive

Description

HENRY is a high-performance wet-set adhesive for installing rubber and vinyl cove base

Use For

Commercial and residential installations of rubber and vinyl cove base.

Bonds To

Structurally sound, clean, smooth, dry wall surfaces. Glazed or metal surfaces must be abraded. Refer to the cove base manufacturer's specific recommendations for suitable substrates.

Preparation

- Acclimate the installation area, adhesive and flooring in an enclosed building at a minimum of 65°F (18°C) for at least 48 hours before, during, and for 48 hours after installation.
- Substrate must be sound, smooth, flat, clean, dry and free of excess moisture and alkali. Remove dirt, wax, grease, paints, oils, sealers, curing compounds and all foreign matter that would interfere with proper adhesion.

Installation

Follow the flooring manufacturer's guidelines for layout and design. Stir any liquid found on the surface into the adhesive, and apply adhesive to the cove base or to the wall using the proper trowel. Stay 1/8" away from the top and bottom of the cove base to prevent the adhesive from oozing. Place cove base into position. Butt the joints neatly. Using a hand roller, roll toward the previously installed section.

11 oz or 30 oz cartridge Directions:

Packaged in a dual-purpose cartridge for your convenience; may be applied with standard closed barrel gun or open barrel skeleton gun.

Closed Barrel Gun: Cut spout about 1/2" from top of tube. Puncture inner seal. Insert cartridge and attach nozzle. Use 2-hole nozzle for 2-1/2" wall base, 3-hole nozzle for 4" wall base, and 5-hole nozzle for 6" wall base.

Skeleton Gun: Cut spout near tip to produce 1/8" bead. Puncture inner seal and insert cartridge. Use two 1/8" beads for 2-1/2" wall base, 3 beads

for 4" wall base and 5 beads for 6" wall base. Be sure to use enough adhesive. Immediately place wall base and roll toward previously installed section using a hand roller.

Clean Up

Remove wet adhesive residue with a clean, white cloth dampened with soapy water. Use mineral spirits for dried adhesive residue, carefully following warnings on the container.

Warranty

10-Year Limited Warranty. For complete warranty details please contact our Customer Service Center 1-800-232-4832.

Notes

Do not reuse container. Dispose of container and adhesive residue in accordance with federal, state and local waste disposal regulations. Do not flush adhesive down drains.

KEEP OUT OF REACH OF CHILDREN.

- Freeze/thaw stable to 10°F (-12°C). Avoid low temperatures or multiple freeze/thaw cycles.
- Shelf life is one year if unopened.
- VOC content: 0 g/L; calculated & reported, SCAQMD 1168

PRECAUTIONS! May be mildly irritating to eyes and skin. May cause allergic respiratory reaction. May cause allergic skin reaction.

Carefully read and follow all cautions and warnings on label or refer to Material Safety Data Sheet for all warnings and additional product information. (www.wwhenry.com)

IMPORTANT TECHNICAL UPDATES

Technical update effective 10-16-18:
ARDEX / HENRY Adhesives and Gypsum Substrates

Made in the USA.
© 2020 ARDEX, L.P. All rights reserved.
Content updated 08-13-2020. Published 10-16-2018. Supersedes all previous versions. Check www.ardexamericas.com for most recent version and for technical updates, which may supersede the information herein.

HT106- 08/2020

ARDEX Americas
400 Ardex Park Drive
Aliquippa, PA 15001 USA
724-203-5000
888-512-7339
www.ardexamericas.com