

## **TECHNICAL DATA SHEET**


### **DESCRIPTION**

The P53 Swift Lift Eye Anchor is designed for use with the P60 Tension Bar placed through the eye of the anchor. This combination of Swift Lift Eye Anchor and P60 Tension Bar allows the anchor's full rated tensile load to be developed in thin, narrow wall applications. The anchor should be located at the center line of the wall. When two or more anchors are required, the minimum spacing between anchors must be equal to the minimum panel width.

#### **APPLICATION**

The Dayton Superior Swift Lift Eye Anchor (P53) is similar to the P52 Anchor but has an eye at the foot to accept P60 Tension Bars. The P53 anchor is used primarily in thin sections, thin panels of lightweight concrete or shapes that must be handled at concrete compressive strengths as low as 2000psi.

Warning: P60 Tension Bar must be used with this anchor to achieve loads.



- Minimum Corner Distance must be at least 1/2 Minimum Panel Width.
- 2 or more anchors require a Minimum Spacing equal to the Minimum Panel Width.

### **FEATURES**

- Available in hot-dipped galvanized for extreme corrosion resistance
- The combination of the P53 Swift Lift Eye Anchor and P60 Tension Bar is an excellent system to use for lifting, handling, and setting precast column and thin walls.

#### **TECHNICAL DATA**

\* Safe Working Load provides a factor of safety of approximately 4 to 1 in 2,000 psi normal weight concrete. The P53 Eye Anchor must be usde in conjunction with the P60 Tension Bar in order to develop its published rated working loads.

Anchor Rated Loads (tons)	Anchor Length (L)	Minimum Thickness or Depth (de)	Actual Edge Distance (de)	Minimum Corner Distance	Minimum Panel Width	Tensile Safe Working Load per Anchor* (lbs)
1	2-1/2"	3"	1-1/2"	8"	16"	2,000
2	3-1/2"	3"	1-1/2"	4"	8"	4,000
4	4-3/4"	3-3/4"	1-7/8"	5"	10"	8,000
8	7-1/16"	4-3/4"	2-3/8"	7"	14"	16,000
20	9-7/8"	6-3/8"	3-3/16"	8-1/2"	17"	40,000

#### **RELATED PRODUCTS**

- P60 Swift Lift® Tension Bar
- P50 Swift Lift® Universal Lifting Eye Hardware
- P56PL Swift Lift® Plus Recess Plug

#### ORDERING INFORMATION

#### SWIFT LIFT® EYE ANCHOR

Product Code	Description	Weight
60683	2 TON SWL 9/16" X 3-1/2" PLAIN	0.34 LB
60686	4 TON SWL 3/4" X 4-3/4" PLAIN	0.94 LB
60689	8 TON SWL 1-3/32" X 7-1/8" PLAIN	2.47 LB
60692	20 TON SWL 1-1/2" X 9-5/8" PLAIN	7.50 LB
60687	4 TON SWL 3/4" X 4-3/4" HDGALV	0.94 LB
101066	8 TON SWL 1-3/32" X 7-1/8" S. STEEL	2.47 LB
126657	8 TON SWL 1-3/32" X 7-1/8" HDGALV	2.50 LB
126861	20 TON SWL 1-1/2" X 9-5/8" HDGALV	7.50 LB

#### **MANUFACTURER**

Dayton Superior Corporation 1125 Byers Road Miamisburg, OH 45342

Customer Service: 888-977-9600 Technical Services: 877-266-7732 Website: www.daytonsuperior.com

Page 1 of 2 File Date: 3/19/2020



# P53 SWIFT LIFT® EYE ANCHOR

Precast / Tilt-Ur

# **TECHNICAL DATA SHEET**

# **WARRANTY (ACCESSORIES)**

Limited Warranty. Dayton warrants, for a period of 60 days from the date of shipment (three years from the date of shipment in the case of formwork, excluding any consumable Products included with such formwork), that Products and any associated application drawings and engineering services provided by Dayton ("Ancillary Services") will be free from defects in material and workmanship and, in the case of custom designed formwork, that the formwork will meet the specifications set forth in the design drawings approved by Dayton and Customer. Any claim under this warranty must be made in writing within such warranty period. If any Product and/or Ancillary Service covered by a timely claim are found to be defective, Dayton will, within a reasonable time, make any necessary repairs or corrections or, at Dayton's option, replace the Product. Unless pre-authorized by Dayton in writing, Dayton will not accept any charges for correcting defects or accept the return of any Product. This warranty will not apply to any Products that have been subjected to misuse, neglect, storage damage, misapplication, accident or any other damage caused by any person other than Dayton, or that have not been maintained in accordance with Dayton's specifications. THIS LIMITED WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES AS TO THE PRODUCTS AND ANCILLARY SERVICES. DAYTON MAKES NO OTHER WARRANTIES OR GUARANTEES, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR OTHERWISE. THE REMEDIES SET FORTH IN THIS SECTION ARE CUSTOMER'S EXCLUSIVE REMEDY FOR BREACH OF WARRANTY.