

Adhesive Anchoring Accessories

PRODUCT DESCRIPTION

Accessories are used in conjunction with various anchoring applications and for supporting proper anchor installation. The accessories are divided into two sections:

Installation Accessories – Tools used to aid in the preparation of the anchor hole and installation.

Screen Tubes – Used with base materials with voids and cavities which require keying action for load transfer. The screen tubes hold the adhesive in place and readily accept threaded rod and reinforcing bar.

SECTION CONTENTS Page No.

Installation Accessories..... 1
Screen Tubes 2

ADHESIVES

INSTALLATION ACCESSORIES

Air Blowers

Cat. No.	Description	Standard Package
08280	Hand Pump / Dust Blower (25 fl. oz. cylinder volume)	1
08292	Air Compressor Nozzle with Extension	1



Nylon Brushes (T308+ and Glass Capsules Only)

Cat. No.	Description	Standard Bag
7931	1/2" x 8-1/2" Nylon Brush	1
7932	3/4" x 8-1/2" Nylon Brush	1
7933	1" x 12" Nylon Brush	1
7934	1-1/4" x 13" Nylon Brush	1
7935	1-1/2" x 13-1/2" Nylon Brush	1



Anchor Seal Plugs

Cat. No.	Description	Plug Depth	Hole Size	Standard Bag
7936	3/8" Anchor Seal Plug	3/8"	7/16"	25
7937	1/2" Anchor Seal Plug	1/2"	9/16"	25



Anchor seal plugs are designed for use as an aid with anchor installation in wall and overhead applications. The plugs help retain the adhesive in the anchor hole and hold the anchor rod centered in the hole until the adhesive sets. The plugs are described by the anchor rod diameter they are used with.

Wire Brushes

Cat No.	Description	Std. Package
08284	Wire brush for 7/16" ANSI hole (3/8" rod or #3 rebar)	1
08285	Wire brush for 9/16" ANSI hole (1/2" rod or #4 rebar)	1
08286	Wire brush for 11/16" ANSI hole (5/8" rod or #5 rebar)	1
08287	Wire brush for 7/8" ANSI hole (3/4" rod or #6 rebar)	1
08288	Wire brush for 1" ANSI hole (7/8" rod or #7 rebar)	1
08289	Wire brush for 1-1/8" ANSI hole (1" rod or #8 rebar)	1
08290	Wire brush for 1-3/8" ANSI hole (1-1/4" rod or #9 rebar)	1
08291	Wire brush for 1-1/2" ANSI hole (#10 rebar)	1
08283	SDS-plus adapter for steel brushes	1
08296	Standard drill adapter for steel brushes (e.g. Jacobs Chuck)	1
08282	Steel brush extension, 12"	1
52073	Adhesive cleaning kit, includes 4 wire brushes (08284, 08285, 08286, 08287), steel brush extension (08282), SDS-plus adapter (08283), standard drill adapter (08296), hand pump/dust blower (08280), gloves and safety glasses	1



Adhesive Piston Plugs

Cat. No.	Description	Drill Diameter	Std. Box.	Std. Ctn.
08300	7/8" Adhesive Piston Plug	7/8"	10	100
08301	1" Adhesive Piston Plug	1"	10	100
08303	1-1/8" Adhesive Piston Plug	1-1/8"	10	100
08305	1-3/8" Adhesive Piston Plug	1-3/8"	10	100
08309	1-1/2" Adhesive Piston Plug	1-1/2"	10	100



b

SCREEN TUBES

Screen tubes should be used with masonry construction when voids are present.

Stainless Steel Screen Tubes (AC100+ Gold and T308+ Only)

Cat. No.	Description	Drill Diameter	Standard Carton
7862	1/4" x 6" Screen Tube*	3/8"	25
7864	1/4" x 8" Screen Tube*	3/8"	25
7961	3/8" x 3 1/2" Screen Tube*	1/2"	25
7962	3/8" x 6" Screen Tube*	1/2"	25
7963	3/8" x 8" Screen Tube*	1/2"	25
7964	3/8" x 10" Screen Tube*	1/2"	25
7959	3/8" x 12" Screen Tube*	1/2"	25
7965	1/2" x 3 1/2" Screen Tube	5/8"	25
7966	1/2" x 6" Screen Tube	5/8"	25
7967	1/2" x 8" Screen Tube*	5/8"	25
7968	1/2" x 10" Screen Tube*	5/8"	25
7969	5/8" x 4 1/2" Screen Tube*	3/4"	20
7970	5/8" x 6" Screen Tube	3/4"	20
7971	5/8" x 8" Screen Tube	3/4"	20
7972	5/8" x 10" Screen Tube	3/4"	20
7973	3/4" x 6" Screen Tube	7/8"	10
7977	3/4" x 8" Screen Tube	7/8"	10
7974	3/4" x 10" Screen Tube	7/8"	10
7975	3/4" x 13" Screen Tube	7/8"	10
7865	15/16" x 8" Screen Tube	1"	10
7867	15/16" x 13" Screen Tube	1"	10
7869	15/16" x 17" Screen Tube	1"	10
7955	13/16" Adhesive Shear Tube (steel sleeve)	Special Order	

Screen tubes are made from a 300 series stainless steel. The nominal diameter of the screen listed indicates the matching rod diameter.

*Includes extension tubing.

Plastic Screen Tubes (AC100+ Gold and T308+ Only)

Cat. No.	Description	Drill Diameter	Standard Carton
8470	1/4" x 1 3/4" Screen Tube	1/2"	25
8473	3/8" x 2 3/4" Screen Tube	9/16"	25
8474	3/8" x 3 1/2" Screen Tube	9/16"	25

The nominal diameter of the screen listed indicates the matching rod diameter. Note that the hole size required for plastic screen tubes are different than that for the stainless steel tubes.



ADHESIVES