

Technical Information Sheet



UltraPly™ QuickSeam™ R.M.A. Strip

Item Description
100 ' (30.5 m) Roll

Item Number

Description

UltraPly QuickSeam R.M.A. Strip is a 10" (254 mm) wide UltraPly TPO membrane with two 3" (76 mm) wide strips of tape factory laminated to it along its length. It is used for roof membrane attachment beneath the UltraPly TPO membrane as additional membrane securement as specified in Elevate specifications and details.

Method of Application

- 1. Unroll the UltraPly QuickSeam R.M.A. Strip with the release paper up.
- 2. Anchor the QuickSeam R.M.A. Strip using Elevate Heavy Duty Seam Plates and Elevate HD Fasteners 12" (305 mm) o.c. per current Elevate specifications and details.
- 3. Position UltraPly TPO membrane over UltraPly QuickSeam R.M.A. Strip with release paper in place and allow membrane to relax.
- 4. Fold back UltraPly TPO membrane to expose the R.M.A. Strip.
- 5. Prime the UltraPly TPO in the area to be spliced to the tape using Single-Ply QuickPrime™ Primer or Single-Ply LVOC Primer, applied with QuickScrubber™ or QuickScrubber Plus pad and handle.
- 6. Use touch-push test to determine when primer is dry and ready to be mated to the tape on the RMA Strip.
- 7. Remove the release paper from the tape.
- 8. Roll the primed UltraPly TPO membrane onto the tape.
- 9. Mate the membrane using a clean QuickScrubber Plus Handle and Pad, then roll the UltraPly TPO membrane over the UltraPly QuickSeam R.M.A. Strip with a 11/2" (38 mm) wide silicone hand roller to ensure proper adhesion.
- 10. Additional information available at Holcim's Technical Database, www.HolcimElevate.com.

Storage

- Store in original unopened containers indoors at temperatures between 60 °F (16 °C) and 80 °F (27 °C).
- Do not store on roof in direct sunlight or at temperatures above 100 °F (38 °C).
- When exposed to lower temperatures; restore to room temperature prior to use.

September 29, 2022

Sales: (800) 428-4442 | Technical (800) 428-4511





Shelf Life

- Shelf life of 24 months can be expected when stored in original container at temperatures between 60 °F (16 °C) and 80 °F (27 °C).
- Shelf life will be shortened if exposed to elevated temperatures.

Precautions

- Do not use UltraPly QuickSeam R.M.A. Strip with UltraPly TPO XR membranes.
- Refer to Safety Data Sheets (SDS) for additional safety information.

LEED® Information

Post-Consumer Recycled Content: 0%

Post Industrial Recycled Content: 0%

Manufacturing Location: Michigan Center, MI





Typical Properties		
Properties	Value	
QuickSeam Tape		
Base	Rubber Polymers	
Color	White	
Solvents	None	
Solids	100%	
Specific Gravity	98 ± 0.02 (H20 =1)	
Cured State	Cured	
Thickness	0.030" (0.76 mm) ± 0.005" (0.13 mm)	
Width	3" (76 mm) -0, + 0.1.25" mm	
Membrane		
Base	ТРО	
Color	White	
Solvents	None	
Thickness	0.050" (1.26 mm) ± 20%	
Width	10" + 0, -0.125" (254 mm) +0, -3.2 mm)	
NOTE: Refer to Tec	hnical Information Sheet for UltraPly TPO	
for additional inform	nation.	

Packaging		
Properties	Value	
Roll	100' (30.5 m) roll	
Carton	1 roll per carton	

Please contact Holcim Technical Services at 800-428-4511 for further information.

This sheet is meant to highlight Elevate products and specifications and is subject to change without notice. Holcim takes responsibility for furnishing quality materials that meet published Elevate product specifications or other technical documents, subject to normal manufacturing tolerances. Neither Holcim nor its representatives practice architecture. Holcim offers no opinion on and expressly refuses any responsibility for the soundness of any structure. Holcim accepts no liability for structural failure or resultant damages. Consult a competent structural engineer prior to installation if the structural soundness or structural ability to properly support a planned installation is in question. No Holcim representative is authorized to vary this disclaimer.

